



## **DPN 760 from Romaco Noack**

Over 700 Romaco Noack DPN 760 machines in operation worldwide are proof of the confidence users in the prescription drugs, generics and contract sectors place in Noack technology. The flexibility of the intermittent motion Romaco Noack DPN 760 provides for both operation on a stand-alone basis or in line with a cartoner.

As a compact, entry-level solution, it is ideal for start-up operations but also offers a number of upgrade options to increase productivity. Its proven technology has been continually enhanced to serve the changing needs of the marketplace, establishing the next generation Romaco Noack DPN 760 as a key choice within the contract and generic markets, where fast changeover, reliability and high availability are essential.

### **Highlights**

- Extremely simple and repeatable operation
- Very small footprint
- Processes all common thermoformable and alu cold forming films
- Powerful PLC with operator-friendly HMI
- Upgrade options include: automatic feeding systems, filling inspection and ejection station, inline foil printer, print mark registration and complete line with a cartoner and end of line equipment
- Ready for Remote Assist
- OPC UA interface for production data acquisition (PDA)

Technical Data	Noack DPN 760
Output blister/minute max.	240
Blister tracks max.	4
Forming cycles/minute max.	60
Cutting cycles/minute max.	60
Foil width max., in mm	165
Forming area max., in mm	155 × 138
Forming depth max., in mm	25
Forming foil reel diameter max., in mm	600
Lidding foil reel diameter max., in mm	300
Machine dimensions (L × W × H), in mm	3,150 × 1,365 × 2,165
Weight, in kg	1,500
Remote Assist connection	Ethernet
PDA interface	OPC UA

Technical changes reserved

